

# wiha Screwdrivers

Tools that work for you

## Speed-E II® Electric Multi-Bit Screwdriver

The Wiha Insulated SpeedE® II electric screwdriver is faster, stronger, and more efficient than ever. The SpeedE® II now features two power levels—0.4 Nm (3.5 in/lbs.) and 1.0 Nm (8.8 in/lbs.)—for an improved range of performance. Upon reaching the torque capacity, simply continue turning fastener by hand using the built-in the ratcheting function to reach the desired tightness and thereby decreasing risk of equipment damage. Change power levels by toggling a switch integrated into the form-fit handle that delivers comfort and control and features a ring light for low-light work environments. Comes with rechargeable lithium-ion batteries for driving up to 800 fasteners per charge—USB charger with plug adapter is included.








## Features

- Two power levels: 0.4 Nm (3.5 in/lbs.) and 1.0 Nm (8.8 in/lbs.) for improved range of performance
- Torque-ratcheting function for hand-finishing fasteners and damage prevention
- Integrated ring-light for low-light work environments
- Rechargeable lithium-ion batteries for driving up to 800 fasteners per charge
- USB connection charger with plug adapter for versatile charging capabilities
- Only compatible with Wiha SlimLine Blades for optimal safety and function
- SlimLine Blades, 33% narrower insulation diameter than standard insulated tools
- ASTM F1505 standard specifications for insulated and insulating hand tools
- CSA testing benchmarks for safety and performance



### Speed-E II® Electric Multi-Bit Screwdriver

Part Number	Number of Pieces	Part Image	Type	Bit Size	Overall Length	Handle Type	Set Includes	Price
<b>WT32490</b>	13		 Phillips	#1 #2	10.25in (260mm)	SoftFinish cushion grip handle	(1) SpeedE II electric handle, (8) SlimLine blades (slotted (3.5mm, 5.5mm), Phillips (#1, #2), square (#1, #2), PlusMinus (#1, #2), (1) adapter plug, (1) battery charger, (2) replaceable lithium-ion batteries, (1) L-Box Mini storage box	\$240.00
			 Slotted	3.5mm 5.5mm				
			 Square	#1 #2				
			 Plus-minus	#1 #2				

# wiha Screwdrivers

Tools that work for you





## PocketMax Multi-Bit Screwdriver









The 6 Piece Insulated SlimLine PocketMax Multi-bit screwdriver is equipped with insulated SlimLine bits. Every single Wiha insulated tool is individually tested to 10,000 volts AC and rated to 1,000 volts AC (1,500 volts DC) for safety and peace of mind in energized applications. Wiha insulated tools are VDE Certified and meet EN/IEC 60900 testing standards for protection against arc flash explosion, ASTM F1505 standard specifications for insulated and insulating hand tools, NFPA-70E standards for electrical safety on the jobsite, and CSA testing benchmarks for safety and performance.



## Features

- SoftFinish® cushion grip handle for comfort and control
- Handle direct molded to blade for permanent bond
- SlimLine blades technology up to 33% narrower insulation diameter, ideal for jobs where access is limited
- Dual durometer construction for long-lasting durability
- Magnetic easy open top with all SlimLine bits secured and stowed away
- Parallel flats for roll-off prevention

PocketMax Multi-Bit Screwdriver								
Part Number	Number of Pieces	Part Image	Type	Tip Size	Overall Length	Handle Type	Set Includes	Price
<a href="#"><u>WT28345</u></a>	6		 Slotted	3.5 mm	6.8in (173mm)	SoftFinish cushion grip handle with bit storage	(1) insulated Pocketmax handle with bit storage, (5) insulated SlimLine bits (slotted: 3.5mm, 6.5mm, Phillips: (#1, #2), square: (#2))	\$53.25
				6.5 mm				
			 Phillips	#1				
				#2				
			 Square	#2				

Multi-Bit Screwdriver Accessories									
Part Number	Part Image	Type	Tip Size	Slotted Tip Thickness	Overall Length	Shaft Length	Shaft Diameter	Fits	Price
<a href="#"><u>WT28310</u></a>		 Slotted	3.5mm	0.6mm	3.0in (76mm)	3.0in (76mm)	0.16in (4.0mm)	SlimLine series handles	\$7.00
<a href="#"><u>WT28315</u></a>			6.5mm	1.2mm			0.24in (6.1mm)		\$7.00
<a href="#"><u>WT28317</u></a>		 Phillips	#1	n/a			0.16in (4.0mm)		\$7.00
<a href="#"><u>WT28319</u></a>			#2				0.24in (6.1mm)		\$7.00
<a href="#"><u>WT28347</u></a>		 Square					\$7.00		