



# Pliers & Cutting Tools

Tools that work for you

## Insulated Pliers

Wiha insulated SoftFinish cushion grip pliers and cutters feature ergonomic cushion grip handles for comfort and control, dual durometer construction for long-lasting durability, and handles directly molded to the tool steel for a permanent bond. The grips feature a slip guard handle design for added protection at the front-end and raised rear-finger steps for easy opening at the back-end. They are individually tested to 10,000 volts AC and rated to 1,000 volts AC (1,500 volts DC) for safety and peace of mind in energized applications. All Wiha insulated tools are VDE Certified and meet EN/IEC 60900 testing standards for protection against arc flash explosion, ASTM F1505 standard specifications for insulated and insulating hand tools, NFPA-70E standards for electrical safety on the job site, and CSA testing benchmarks for safety and performance.

## Features

- Individually tested to 10,000 volts AC and rated to 1,000 volts AC for safety and peace of mind
- Induction-hardened cutting edges and jaws for superior sharpness and longevity, approximately 64HRC
- Standard industrial brushed finish for surface endurance
- Slip guard handle design for added protection
- Premium quality C70 tool steel for strength and durability
- Heavy duty steel riveted joints to withstand high load levels



Insulated Pliers												
Part Number	Part Image	Pliers Type	Handle Type	Overall Length	Handle Length	Jaw Length	Jaw Opening	Jaw Thickness	Jaw Width	Material	Capacity	Price
<a href="#"><u>WT32923</u></a>		Long Nose	Insulated cushion grip handles	8.0in (203mm)	4.4in (112mm)	2.75in (69.9mm)	3.08in (78.2mm)	0.42in (10.7mm)	0.75in (19.1mm)	C70 Steel	8 AWG	\$36.00
<a href="#"><u>WT32926</u></a>				6.3in (160mm)	3.9in (99mm)	1.87in (47.5mm)	2.17in (55.1mm)	0.35in (8.9mm)	0.69in (17.5mm)		10 AWG	\$28.75
<a href="#"><u>WT32928</u></a>		Bent Nose				1.77in (45.0mm)	1.70in (43.2mm)		0.67in (17.0mm)		n/a	Retired
<a href="#"><u>WT32930</u></a>		Combination		8.0in (203mm)	6.0in (152mm)	1.80in (45.7mm)	1.91in (48.5mm)	0.59in (15.0mm)	1.16in (29.5mm)		4 AWG	\$36.00
<a href="#"><u>WT32941</u></a>		Long Flat Nose		6.3in (160mm)	3.9in (99mm)	2.00in (50.8mm)	2.32in (58.9mm)	0.24in (6.0mm)	0.67in (17.0mm)		n/a	\$27.50
<a href="#"><u>WT32947</u></a>		Wire Stripping			4.4in (112mm)	1.28in (32.5mm)	1.59in (40.4mm)	0.36in (9.1mm)	1.49in (37.8mm)		28-8 AWG	\$30.75
<a href="#"><u>WT32954</u></a>		Tongue and Groove			4.7in (119mm)		2.00in (50.8mm)	0.28in (7.1mm)	0.27in (6.9mm)		n/a	\$39.00