

wiha SoftFinish Insulated Screwdrivers

Tools that work for you

Insulated Screwdrivers








Wiha Insulated SoftFinish® Cushion Grip screwdrivers consist of Wiha engineered premium quality tool steel for strength and durability, have black oxide finish for corrosion protection, and feature exact fit precision machined tips for reduced cam-out. All Wiha insulated screwdrivers are VDE Certified and meet EN/IEC 60900 testing standards for protection against arc flash explosion, ASTM F1505 standard specifications for insulated and insulating hand tools, NFPA-70E standards for electrical safety on the jobsite, and CSA testing benchmarks for safety and performance. SoftFinish® driver handles feature an 8-edged large-diameter comfort grip for maximum gripping area, giving the user powerful torque and less fatigue.



WT32091

Features

- Ergonomic cushion grip handle for comfort and control
- Dual durometer construction for long-lasting durability
- Handle directly molded to the blade for permanent bond
- Handle size proportionate to blade for consistent mechanical advantage
- Parallel flats for roll-off prevention
- Tip profile labeled on cap for easy identification
- Wiha premium quality tool steel for strength and durability
- Black oxide finish for corrosion protection
- Exact fit precision machined tip for reduced cam-out
- Individually tested to 10,000 volts AC and rated to 1,000 volts AC for safety and peace of mind

Insulated Screwdrivers											
Part Number	Part Image	Type	Tip Size	Slotted Tip Thickness	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Insulation Rating	Price
<u>WT32005</u>		● Slotted	2.0mm	0.4mm	6.5in (165mm)	2.4in (60mm)	0.20in (5.1mm)	4.1in (104mm)	SoftFinish cushion grip handle	1000V	\$6.25
<u>WT32010</u>			2.5mm		7.1in (180mm)	3.0in (75mm)	0.22in (5.6mm)				\$6.25
<u>WT32012</u>			3.0mm	0.6mm	8.0in (203mm)	3.9in (100mm)	0.27in (6.9mm)				\$6.25
<u>WT32015</u>			3.5mm					\$6.75			
<u>WT32017</u>			4.0mm	0.8mm	8.3in (211mm)	4.4in (112mm)	0.29in (7.3mm)	\$8.00			
<u>WT32024</u>			4.5mm	1.0mm	9.3in (236mm)		4.9in (125mm)	0.32in (8.1mm)			\$8.25
<u>WT32039</u>			6.5mm	1.2mm	10.6in (269mm)		5.9in (150mm)	0.38in (9.7mm)			4.7in (119mm)



SoftFinish Insulated Screwdrivers

Tools that work for you

Insulated Screwdrivers - Cont'd											
Part Number	Part Image	Type	Tip Size	Slotted Tip Thickness	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Insulation Rating	Price
<u>WT32046</u>		● Slotted	3.5mm	0.6mm	8.0in (203mm)	3.9in (100mm)	0.14in (3.5mm)	4.1in (104mm)	SoftFinish cushion grip handle	1000V	\$12.25
<u>WT32049</u>			4mm	0.8mm	8.3in (211mm)		0.16in (4.0mm)	4.4in (112mm)			\$14.00
<u>WT32023</u>			4.5mm	1.0mm			0.24in (6.1mm)	4.7in (119mm)			\$7.75
<u>WT32052</u>					0.18in (4.6mm)	3.4in (86mm)	\$14.00				
<u>WT32055</u>			5.5mm	9.6in (243mm)	4.9in (125mm)	0.22in (5.6mm)	4.5in (114mm)	\$15.00			
<u>WT32031</u>			11.5in (292mm)	6.9in (175mm)	0.28in (7.0mm)	\$8.50					
<u>WT32026</u>					4.5in (114mm)	\$8.75					
<u>WT32034</u>			6mm	10.6in (269mm)	5.9in (150mm)	0.30in (7.6mm)	4.7in (119mm)	\$10.75			
<u>WT32058</u>			6.5mm			0.26in (6.5mm)		\$18.00			



SoftFinish Insulated Screwdrivers







Tools that work for you

Insulated Screwdrivers - Cont'd										
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Insulation Rating	Price
WT32100		+ Phillips	#0	6.5in (165mm)	2.4in (60mm)	0.25in (6.4mm)	4.1in (104mm)	SoftFinish cushion grip handle	1000V	\$6.75
WT32101			#1	7.5in (191mm)	3.1in (80mm)	0.30in (7.6mm)	4.4in (112mm)			\$8.00
WT32145				8.0in (203mm)		0.18in (4.6mm)	4.9in (124mm)			\$14.00
WT32146			#2	8.3in (211mm)	3.9in (100mm)	0.24in (6.1mm)	4.4in (112mm)			\$17.00
WT32102				8.6in (218mm)		0.35in (8.9mm)	4.7in (119mm)			\$9.75
WT32103			#3	10.6in (269mm)	6.0in (150mm)					\$14.25
WT32505		+ Torx	T5			0.45in (11.4mm)				\$7.00
WT32531			T10				4.1in (104mm)			\$7.00
WT32521			T8	6.5in (165mm)	2.4in (60mm)					\$6.75
WT32526			T9			0.18in (4.6mm)				\$6.75
WT32536			T15				4.4in (112mm)			\$8.25
WT32541			T20	7.5in (191mm)	3.1in (80mm)	0.24in (6.1mm)				\$8.50
WT32546			T25	7.8in (198mm)				\$8.50		
WT32551			T27				4.7in (119mm)	\$10.50		
WT32556			T30	8.6in (218mm)	3.9in (100mm)	0.30in (7.6mm)		\$10.50		



SoftFinish Insulated Screwdrivers

Tools that work for you

Insulated Screwdrivers - Cont'd										
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Insulation Rating	Price
WT30746		⊕ Plus-minus	#1	7.5in (191mm)	3.1in (80mm)	0.18in (4.6mm)	4.4in (112mm)	SoftFinish cushion grip handle	1000V	\$15.25
WT30702						0.24in (6.1mm)				\$8.50
WT30747			#2	8.6in (218mm)	3.9in (100mm)	0.24in (6.1mm)	4.7in (119mm)			\$19.00
WT30704						0.30in (7.6mm)				\$10.25
WT35811		⊞ Square	#1	8.2in (210mm)	5.9in (150mm)	0.22in (5.6mm)	4.3in (109mm)			\$8.50
WT35812			#2	10.6in (269mm)		0.25in (6.4mm)	4.7in (119mm)			\$10.25



Tools that work for you

SoftFinish Insulated Screwdriver and Nutdriver Sets

Insulated Screwdrivers

Wiha Insulated SoftFinish® Cushion Grip screwdrivers consist of Wiha engineered premium quality tool steel for strength and durability, have black oxide finish for corrosion protection, and feature exact fit precision machined tips for reduced cam-out. All Wiha Insulated screwdrivers are VDE Certified and meet EN/IEC 60900 testing standards for protection against arc flash explosion, ASTM F1505 standard specifications for insulated and insulating hand tools, NFPA-70E standards for electrical safety on the jobsite, and CSA testing benchmarks for safety and performance. SoftFinish® driver handles feature an 8-edged large-diameter comfort grip for maximum gripping area, giving the user powerful torque and less fatigue.



WT32091

Features

- Ergonomic cushion grip handle for comfort and control
- Dual durometer construction for long-lasting durability
- Handle directly molded to the blade for permanent bond
- Handle size proportionate to blade for consistent mechanical advantage
- Parallel flats for roll-off prevention
- Tip profile labeled on cap for easy identification
- Wiha premium quality tool steel for strength and durability
- Black oxide finish for corrosion protection
- Exact fit precision machined tip for reduced cam-out
- Individually tested to 10,000 volts AC and rated to 1,000 volts AC for safety and peace of mind

Insulated Screwdriver and Nutdriver Sets							
Part Number	Number of Pieces	Part Image	Type	Tip Size	Insulation Rating	Set Includes	Price
<u>WT32091</u>	5		⊕ Phillips	#1 #2	1000V	(5) insulated SoftFinish screwdrivers (Phillips #1, #2, slotted 3.0mm, 4.5mm, 6.5mm)	\$42.25
			⊖ Slotted	3.0mm 4.5mm 6.5mm			
<u>WT32099</u>	7		⊕ Phillips	#1 #2 #3	1000V	(7) insulated SoftFinish screwdrivers (Phillips #1, #2, #3, slotted 3.0mm, 4.0mm, 5.5mm, 6.5mm)	\$63.25
			⊖ Slotted	3.0mm 4.0mm 5.5mm 6.5mm			
<u>WT32059</u>	5		⊕ Phillips	#1 #2	1000V	(5) insulated SoftFinish screwdrivers (Phillips: (#1, #2), slotted (4.5mm, 6.5mm), square: (#2))	\$39.50
			⊖ Slotted	4.5mm 6.5mm			
			⊠ Square	#2			
<u>WT32090</u>	4		⊕ Phillips	#1 #2	1000V	(4) insulated SoftFinish screwdrivers (slotted: (3.5mm, 4.5mm), Phillips: (#1 #2))	\$31.00
			⊖ Slotted	3.5mm 4.5mm			
<u>WT32092</u>	6		⊕ Phillips	#1 #2 #3	1000V	(6) insulated SoftFinish screwdrivers (slotted: (3.5mm, 4.5mm, 6.5mm), Phillips: (#1, #2, #3))	\$55.00
			⊖ Slotted	3.5mm 4.5mm 6.5mm			



SoftFinish Insulated Screwdriver and Nutdriver Sets

Insulated Screwdriver and Nutdriver Sets - Cont'd							
Part Number	Number of Pieces	Part Image	Type	Tip Size	Insulation Rating	Set Includes	Price
WT32093	10		<ul style="list-style-type: none"> Phillips Slotted 	<ul style="list-style-type: none"> #0 #1 #2 #3 2.0mm 2.5mm 3.0mm 3.5mm 4.5mm 6.5mm 	1000V	(10) insulated SoftFinish screwdrivers (slotted: (2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.5mm, 6.5mm), Phillips: (#0, #1, #2, #3))	\$81.00
WT32094	13		<ul style="list-style-type: none"> Phillips Slotted 	<ul style="list-style-type: none"> #0 #1 #2 #3 2.0mm 2.5mm 3.0mm 3.5mm 4.5mm 5.5mm 6.5mm 8.0mm 10.0mm 		(13) insulated SoftFinish screwdrivers (slotted: (2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.5mm, 5.5mm, 6.5mm, 8.0mm, 10.0mm), Phillips: (#0, #1, #2, #3))	\$120.00
WT32097	7		<ul style="list-style-type: none"> Phillips Slotted Square 	<ul style="list-style-type: none"> #1 #2 3.5mm 5.5mm 6.5mm #1 #2 		(7) insulated SoftFinish screwdrivers (slotted: (3.5mm, 5.5mm, 6.5mm), Phillips: (#1, #2), square: (#1, #2))	\$51.00
WT32188	7		<ul style="list-style-type: none"> Phillips Slotted 	<ul style="list-style-type: none"> #0 #1 2.0mm 2.5mm 3.0mm 3.5mm 4.0mm 		(7) insulated SoftFinish screwdrivers (slotted: (2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.0mm), Phillips: (#0, #1)), plastic molded case	\$59.00
WT32190	15		<ul style="list-style-type: none"> Phillips Slotted Internal Hex 	<ul style="list-style-type: none"> #1 #2 #3 2.0mm 2.5mm 3.0mm 3.5mm 4.5mm 6.5mm 8.0mm 1/4in 5/16in 3/8in 7/16in 1/2in 		(10) insulated SoftFinish screwdrivers (slotted: (2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.5mm, 6.5mm, 8.0mm), Phillips: (#1, #2, #3)), (5) insulated SoftFinish nut drivers (1/4in, 5/16in, 3/8in, 7/16in, 1/2in), fold out carry case	\$200.00
WT32196	6		<ul style="list-style-type: none"> Phillips Slotted Square 	<ul style="list-style-type: none"> #1 #2 4.5mm 6.5mm #1 #2 		(6) insulated SlimLine SoftFinish screwdrivers (slotted: (4.5mm, 6.5mm), Phillips: (#1, #2), square: (#1, #2))	\$56.00



SoftFinish Insulated Screwdriver and Nutdriver Sets

Insulated Screwdriver and Nutdriver Sets - Cont'd							
Part Number	Number of Pieces	Part Image	Type	Tip Size	Insulation Rating	Set Includes	Price
<u>WT32197</u>	8		⊕ Phillips	#1 #2	1000V	(8) insulated SlimLine SoftFinish screwdrivers (slotted: (3.5mm, 4.0mm, 4.5mm, 5.5mm), Phillips: (#1, #2), square (#1, #2))	\$120.00
			◐ Slotted	3.5mm 4.0mm 4.5mm 5.5mm			
			◑ Square	#1 #2			
<u>WT32198</u>	11		⊕ Phillips	#1 #2	1000V	(11) insulated SlimLine SoftFinish screwdrivers (slotted: (3.5mm, 4.0mm, 4.5mm, 5.5mm, 6.5mm), Phillips: (#1, #2), PlusMinus: (#1, #2), square: (#1, #2))	\$102.00
			◐ Slotted	3.5mm 4.0mm 4.5mm 5.5mm 6.5mm			
			◑ Square	#1 #2			
			⊕ Plus-minus	#1 #2			
<u>WT32293</u>	7		⦿ Internal Hex	5.0mm 6.0mm 7.0mm 8.0mm 9.0mm 10.0mm 11.0mm 12.0mm 13.0mm	1000V	(7) insulated SoftFinish nut drivers (5.0mm, 6.0mm, 7.0mm, 8.0mm, 9.0mm, 10.0mm, 11.0mm, 12.0mm, 13.0mm)	\$91.00
<u>WT32294</u>	7		⦿ Internal Hex	3/16in 7/32in 1/4in 5/16in 3/8in 7/16in 1/2in	1000V	(7) insulated SoftFinish nut drivers (3/16in, 7/32in, 1/4in, 5/16in, 3/8in, 7/16in, 1/2in)	\$91.00
<u>WT32590</u>	6		⊕ Torx	T8 T9 T10 T15 T20 T25	1000V	(6) insulated SoftFinish screwdrivers (torx: (T8, T9, T10, T15, T20, T25))	\$45.00
<u>WT35890</u>	6		⊕ Phillips	#1 #2	1000V	(6) insulated SoftFinish screwdrivers (slotted: (4.5mm, 6.5mm), Phillips: (#1, #2), square: (#1, #2))	\$54.00
			◐ Slotted	4.5mm 6.5mm			
			◑ Square	#1 #2			