

wiha Pliers

Tools that work for you









Pliers

Wiha's pliers feature soft vinyl handles for comfort and control. Every plier is constructed of premium quality tool steel with induction-hardened jaws and cutting edges for superior sharpness and service life. Experience 40% more gripping power with Wiha's patented DynamicJoint pliers, designed to reduce hand fatigue and make your job easier.

Features

- Wiha patented DynamicJoint for 40% stronger grip and easier cuts
- Induction-hardened cutting edges and jaws for superior sharpness and longevity
- Slip guard handle design for added protection
- Heavy-duty steel riveted joints to withstand high load levels



| Pliers | | | | | | | | | | | | |
|-------------------------|-------------------------------------------------------------------------------------|-------------------|-----------------------------|-------------------|------------------|--------------------|--------------------|--------------------|--------------------|-----------|-----------------------------|---------|
| Part Number | Part Image | Pliers Type | Handle Type | Overall Length | Handle Length | Jaw Length | Jaw Opening | Jaw Thickness | Jaw Width | Material | Capacity | Price |
| WT30905 |  | Combination | Industrial SoftGrip handles | 8.0in (203mm) | 5.7in (145mm) | 2.69in (68.3mm) | 1.80in (45.7mm) | 0.46in (11.7mm) | 1.10in (27.9mm) | C70 Steel | 7 AWG | \$30.75 |
| WT32616 |  | Linesman's | Classic grip vinyl handles | 9.0in (229mm) | 4.9in (124mm) | 1.80in (45.7mm) | 1.91in (48.5mm) | 0.59in (15.0mm) | 1.16in (29.5mm) | | 4 AWG | \$41.25 |
| WT32621 |  | Long Nose | | 8.0in (203mm) | 3.0in (76mm) | 2.75in (69.9mm) | 3.08in (78.2mm) | 0.42in (10.7mm) | 0.75in (19.1mm) | | 8 AWG | \$22.75 |
| WT32624 |  | Linesman's | | 9.5in (241mm) | 5.7in (145mm) | 1.60in (40.6mm) | 2.00in (50.8mm) | 0.35in (8.9mm) | 1.30in (33.0mm) | | n/a | \$29.50 |
| WT32637 |  | Tongue and Groove | | 10.0in (254mm) | 5.2in (132mm) | 1.25in (31.8mm) | 1.50in (38.1mm) | 0.25in (6.4mm) | 1.13in (28.7mm) | | 1.5in round 1-9/16in hex | \$34.25 |
| WT32661 |  | | | 10.0in (254mm) | 4.1in (104mm) | 2.30in (58.4mm) | 3.30in (83.8mm) | 0.28in (7.1mm) | 1.11in (28.2mm) | | 1.75in round 2.0in hex | \$30.75 |
| WT32635 |  | | | 10.3in (262mm) | 4.7in (119mm) | 1.00in (25.4mm) | 1.65in (41.9mm) | 0.32in (8.1mm) | 1.56in (39.6mm) | | n/a | \$51.50 |
| WT32636 |  | | | Diagonal | 8.0in (203mm) | 6.0in (152mm) | 0.90in (22.9mm) | 0.50in (12.7mm) | 0.54in (13.7mm) | | 1.16in (29.5mm) | n/a |