







wiha Pliers & Cutting Tools








Tools that work for you

Pliers Sets

Pliers Sets							
Part Number	Number of Pieces	Part Image	Set Type	Pliers Type	Capacity	Set Includes	Price
<u>WT32601</u>	4		Pliers set	Combination Long Nose Tongue and Groove Diagonal	10 AWG	(1) combination pliers 8in, (1) long nose pliers w/ cutters 6.3in, (1) diagonal cutters 6.3in, (1) V-Jaw tongue and groove pliers 10in, roll-up tool pouch	\$89.50
<u>WT32608</u>	8			Combination Long Nose Long Flat Nose Long Round Nose Diagonal High Leverage Diagonal	4 AWG	(1) combination pliers 6.3in, (1) high leverage combination pliers 9in, long nose pliers w/ cutters 6.3in, (1) long nose pliers w/ cutters 8in, (1) long flat nose pliers 6.3in, (1) long round nose pliers 6.3in, (1) diagonal cutters 6.3in, (1) high leverage diagonal cutters 8in, (1) pouch canvas	\$170.75
<u>WT32626</u>	5			Internal Snap Ring	n/a	(5) classic grip internal ring pliers (12.2in - 3.2mm tip, 5.5in - 0.9mm tip, 5.5in - 1.3mm tip, 7in - 1.5mm tip, 8.9in - 2.3mm tip)	\$133.75
<u>WT32634</u>	3		Pliers and cutters set	Long Nose High Leverage Diagonal Linesman's	4 AWG	(1) classic grip long nose pliers 8in, (1) high leverage diagonal cutters 8in, (1) NE Style Lineman's Pliers 9.5in	\$72.00
<u>WT32647</u>	4			Combination Long Nose Tongue and Groove Diagonal	8 AWG	(1) classic grip combination pliers 8in, (1) classic grip long nose pliers w/ cutters 8in, classic grip diagonal cutter 6.3in, classic grip V-jaw tongue and groove pliers 10in	\$115.00
<u>WT32648</u>	2			Long Nose Diagonal		(1) classic grip long nose pliers w/ cutters 8in, (1) classic grip diagonal cutters 6.3in	\$44.25

wiha Pliers & Cutting Tools

Tools that work for you

Pliers Sets - cont'd							
Part Number	Number of Pieces	Part Image	Set Type	Pliers Type	Capacity	Set Includes	Price
<u>WT32653</u>	3		Pliers and cutters set	Combination Long Nose High Leverage Diagonal	4 AWG	(1) classic grip combination pliers 8in, (1) classic grip long nose pliers w/ cutters 8in, classic grip high leverage diagonal cutter 8in, belt pack pouch	\$77.25
<u>WT32669</u>			Pliers set	Adjustable Push Button	n/a	(3) V-jaw tongue and groove adjustable push button pliers (7in, 10in, 12in)	\$103.00
<u>WT32670</u>				Tongue and Groove		(3) V-jaw tongue and groove pliers (7in, 10in, 12in)	\$92.50
<u>WT32698</u>			Pliers and cutters set	Combination Long Nose Diagonal	10 AWG	(1) classic grip combination pliers 7in, (1) classic grip long nose pliers w/cutters 6.3in, (1) classic grip diagonal cutters 6.3in	\$60.50
<u>WT32699</u>	2		Pliers set	Long Nose Linesman's	8 AWG	(1) long nose pliers 8in, (1) NE style lineman's pliers 9.5in	\$60.50
<u>WT32968</u>	3		Pliers and cutters set	Long Nose Linesman's High Leverage Diagonal	4 AWG	(1) industrial long nose pliers 8in (1) NE style lineman's pliers 9.5in, (1) industrial high leverage diagonal cutters 8in	\$113.25
<u>WT57830</u>	3		Pliers set	Wire Stripping Crimping Wire Cutting	22-10 AWG	(1) classic grip wire combination strippers/crimpers 8.25in, 10AWG max capacity, (1) classic grip wire strippers and cutters 6in, 10AWG max capacity, (1) classic grip wire stripper dual NM-B cable 7.75in, 12AWG max capacity	\$70.00