

wiha Screwdrivers

Tools that work for you

Precision Screwdrivers

Wiha Precision Screwdrivers feature cushion-grip handles for comfort and control, and the dual durometer material is direct molded to the blade for a permanent bond. The Precision style includes a hex profile finger grip for precise torque and a tapered handle for rapid rotation. The handles are sized proportionate to the tip and feature an extra-long handle with a smooth-turning cap for multiple hand positions. The driver tip profiles are labeled on the handle to quickly and easily identify the driver.



Features

- Handle direct molded to blade for a permanent bond
- Tapered handle for rapid rotation
- Extra-long handle for optimal hand positions and smooth turning
- Tip profile labeled on handle for easy identification
- Handle sized proportionate to the blade for consistent mechanical advantage
- Wiha engineered premium quality tool steel for strength and durability
- Chrome-plated satin finish for corrosion protection
- Exact fit precision machined tip for reduced cam-out

Precision Screwdrivers											
Part Number	Part Image	Type	Tip Size	Slotted Tip Thickness	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price	
WT26008		 Slotted	0.8mm	0.16mm	4.7in (119mm)	1.6in (40mm)	0.08in (2.0mm)	3.1in (79mm)	Cushion grip handle with rotating cap	\$7.00	
WT26010			1.0mm	0.18mm						\$6.50	
WT26012			1.2mm	0.2mm						\$5.50	
WT26015			1.5mm	0.25mm						\$5.00	
WT26018			1.8mm	0.3mm						\$5.00	
WT26020			2.0mm	0.4mm	5.7in (145mm)	2.0in (50mm)		3.7in (94mm)		\$4.75	
WT26022										\$4.75	
WT26023										\$4.75	



Tools that work for you

Precision Screwdrivers - Cont'd											
Part Number	Part Image	Type	Tip Size	Slotted Tip Thickness	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price	
<u>WT26025</u>		 Slotted	2.5mm	0.4mm	5.7in (145mm)	2.0in (50mm)	0.10in (2.5mm)	3.7in (94mm)	Cushion grip handle with rotating cap	\$4.50	
<u>WT26027</u>					7.7in (196mm)	3.9in (100mm)		3.8in (97mm)		\$4.50	
<u>WT26028</u>					9.6in (243mm)	5.9in (150mm)		3.7in (94mm)		\$5.50	
<u>WT26030</u>			3.0mm	0.5mm	5.7in (145mm)	2.0in (50mm)	0.12in (3.0mm)	3.7in (94mm)		\$4.25	
<u>WT26032</u>					6.7in (170mm)	2.4in (60mm)		4.3in (109mm)		\$4.50	
<u>WT26033</u>					8.3in (211mm)	3.9in (100mm)		4.4in (112mm)		\$5.00	
<u>WT26034</u>					10.2in (259mm)	5.9in (150mm)		4.4in (112mm)		\$5.75	
<u>WT26035</u>			3.5mm	0.6mm	6.7in (170mm)	2.4in (60mm)	0.14in (3.5mm)	4.3in (109mm)		\$4.75	
<u>WT26040</u>			4.0mm	0.8mm				4.3in (109mm)		\$5.25	
<u>WT26041</u>					8.3in (211mm)	3.9in (100mm)	0.16in (4.0mm)	4.4in (112mm)		\$5.00	
<u>WT26042</u>					10.2in (259mm)	5.9in (150mm)	4.3in (109mm)			\$6.00	
<u>WT26074</u>			3.5mm	0.6mm	6.3in (160mm)	2.4in (60mm)	0.14in (3.5mm)	3.9in (99mm)		\$6.25	



Tools that work for you

Precision Screwdrivers - Cont'd									
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price
<u>WT26102</u>		⊕ Phillips	#000	4.7in (119mm)	1.6in (40mm)	0.08in (2.0mm)	3.1in (79mm)	Cushion grip handle with rotating cap	\$6.75
<u>WT26100</u>			#00						\$5.25
<u>WT26105</u>			#0	5.7in (145mm)	2.0in (50mm)	0.12in (3.0mm)	3.7in (94mm)		\$4.75
<u>WT26108</u>				6.7in (170mm)	3.0in (75mm)				\$4.50
<u>WT26109</u>				9.6in (243mm)	5.9in (150mm)				\$6.00
<u>WT26110</u>			#1	6.7in (170mm)	2.4in (60mm)	0.16in (4.0mm)	4.3in (109mm)		\$5.00
<u>WT26115</u>				10.2in (259mm)	5.9in (150mm)				\$6.25



Tools that work for you

Precision Screwdrivers - Cont'd									
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price
<u>WT26307</u>		 External Hex	0.7mm (.028in)	4.7in (119mm)	1.6in (40mm)	0.10in (2.5mm)	3.1in (79mm)	Cushion grip handle with rotating cap	\$5.00
<u>WT26309</u>			0.9mm (.035in)						\$5.00
<u>WT26313</u>			1.3mm (.050in)						\$4.75
<u>WT26315</u>			1.5mm	5.7in (145mm)	2.0in (50mm)	0.09in (2.3mm)	3.7in (94mm)		\$4.75
<u>WT26316</u>			1/16in						\$4.25
<u>WT26320</u>			2.0mm (5/64in)						\$4.25
<u>WT26323</u>			3/32in	6.7in (170mm)	2.4in (60mm)	0.11in (2.9mm)	4.3in (109mm)		\$4.00
<u>WT26325</u>			2.5mm						\$4.25
<u>WT26326</u>			7/64in			0.12in (3.0mm)			\$3.75
<u>WT26334</u>			3mm			0.14in (3.5mm)			\$3.75
<u>WT26335</u>			1/8in			0.15in (3.8mm)			\$3.75

wiha Screwdrivers

Tools that work for you

Precision Screwdriver Sets

Wiha Precision Screwdrivers feature cushion-grip handles for comfort and control, and the dual durometer material is direct-molded to the blade for a permanent bond. The precision style includes a hex profile finger grip for precise torque and a tapered handle for rapid rotation. The handles are sized proportionate to the tip and feature an extra-long handle with a smooth-turning cap for multiple hand positions.

Features

- Handle direct molded to blade for a permanent bond
- Tapered handle for rapid rotation
- Extra-long handle for optimal hand positions and smooth turning
- Tip profile labeled on handle for easy identification
- Handle sized proportionate to the blade for consistent mechanical advantage
- Wiha engineered premium quality tool steel for strength and durability
- Chrome-plated satin finish for corrosion protection
- Exact fit precision machined tip for reduced cam-out



Precision Screwdriver Sets						
Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
<u>WT26090</u>	6		 Slotted	1.5mm 2mm 2.5mm 3mm 3.5mm 4mm	(6) precision screwdrivers (slotted: (1.5mm, 2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.0mm))	\$27.00
<u>WT26092</u>	7		 Phillips  Slotted	#0 2.5mm 3mm 4mm	(7) precision screwdrivers (slotted: (2.5 x 50mm, 2.5, 3.0, 4.0 x 100mm, 3.0, 4.0 x 150mm), Phillips (#0 x 75mm))	\$33.00
<u>WT26098</u>	8		 Slotted	1mm 1.2mm 1.5mm 2mm 2.5mm 3mm 3.5mm 4mm	(8) precision screwdrivers (slotted: (1.0mm, 1.2mm, 1.5mm, 2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.0mm)), canvas pouch.	\$42.00
<u>WT26192</u>	5		 Phillips  Slotted	#0 #1 2.5mm 3.0mm 4.0mm	(5) precision screwdrivers (slotted: (2.5mm, 3.0mm, 4.0mm), Phillips: (#0, #1))	\$30.00
<u>WT26194</u>	4		 Phillips	#000 #00 #0 #1	(4) precision screwdrivers (Phillips: (#000, #00, #0, #1))	\$20.00
<u>WT26197</u>	7		 Phillips  Slotted	#00 #0 #1 1.5mm 2.0mm 2.5mm 3.0mm	(7) precision screwdrivers (Phillips: (#00, #0, #1), slotted (1.5mm, 2.0mm, 2.5mm, 3.0mm))	\$31.00
<u>WT26199</u>	8		 Phillips  Slotted	#000 #00 #0 #1 1.0mm 2.0mm 3.0mm 4.0mm	(8) precision screwdrivers (slotted: (1.0mm, 2.0mm, 3.0mm, 4.0mm), Phillips: (#000, #00, #0, #1)), canvas pouch	\$45.00

Precision Screwdriver - Cont'd						
Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
<u>WT26390</u>	7		External Hex	0.7mm 0.9mm 1.3mm 1.5mm 2mm 2.5mm 3mm	(7) precision screwdrivers (hex: (0.7mm, 0.9mm, 1.3mm, 1.5mm, 2.0mm, 2.5mm, 3.0mm))	\$31.00
<u>WT26391</u>	8			0.028in 0.035in 0.050in 1/16in 5/64in 3/32in 7/64in 1/8in	(8) precision screwdrivers (hex: (0.028in, 0.035in, 0.050in, 1/16in, 5/64in, 3/32in, 7/64in, 1/8in))	\$35.00
<u>WT26491</u>	5		Ball-end Hex	1.35mm 1.5mm 2mm 2.5mm 3mm	(5) precision screwdrivers (ball end hex: (1.35mm, 1.5mm, 2.0mm, 2.5mm, 3.0mm))	\$26.00
<u>WT26791</u>	8		Torx	T1 T2 T3 T4 T5 T6 T7 T8	(8) precision screwdrivers (torx: (T1, T2, T3, T4, T5, T6, T7, T8))	\$48.00
<u>WT26799</u>	8			T3 T4 T5 T6 T7 T8 T9 T10	(8) precision screwdrivers (torx: (T3, T4, T5, T6, T7, T8, T9, T10)), roll up pouch	\$54.00