

# wiha Screwdrivers

Tools that work for you

## Drive-Loc Screwdrivers

Wiha SoftFinish® Drive-Loc Screwdrivers are some of the most versatile screwdrivers on the planet. The Drive-Loc system allows for professionals to continuously adjust shaft length. Short or long, Drive-Loc is built for any application. The Drive-Loc system quickly locks in place in 1/8 in increments, allowing for unprecedented flexibility.

## Features

- SoftFinish® cushion grip handle for comfort and control
- Drive-Loc VI features adjustable/reversible locking blades
- Blades made of high-performance CRM-72 tool steel
- 8-edged soft-grip maximizes turn force for 40% more power
- Selectable lengths (1.7 in – 4.8 in) in 1/8 in increments
- Tip profile labeled on cap for easy identification

**WT28188**

| Drive-Loc Sets |                  |                                                                                     |                                                                                                      |                                                                                                                                   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |          |
|----------------|------------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| Part Number    | Number of Pieces | Part Image                                                                          | Type                                                                                                 | Tip Size                                                                                                                          | Set Includes                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    | Price    |
| <b>WT28188</b> | 32               |  |  Phillips         | #0<br>#1<br>#2                                                                                                                    | (1) SoftFinish Drive-Loc VI handle, (17) Drive-Loc VI adjustable/reversible blades (Phillips (#0, #1, #2), slotted (3.0mm, 3.5mm, 4.0mm, 4.5mm, 5.5mm, 6.0mm, 6.5mm), square (#1, #2), Tamperproof Torx T6, T7, T8, T9, T10, T15, T20, T25, T30, T40), hex (3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 2.0mm, 2.5mm, 3.0mm, 4.0mm, 5.0mm, 6.0mm), (14) Drive-Loc VI adjustable nut drivers (1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 7/16in, 1/2in, 5.5mm, 6.0mm, 7.0mm, 8.0mm, 9.0mm, 10.0mm, 11.0mm), 38 Position Wiha red and black wallet | \$309.00 |
|                |                  |                                                                                     |  Slotted          | 3.0mm<br>3.5mm<br>4.0mm<br>4.5mm<br>5.5mm<br>6.0mm<br>6.5mm                                                                       |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |          |
|                |                  |                                                                                     |  Tamperproof Torx | T6<br>T7<br>T8<br>T9<br>T10<br>T15<br>T20<br>T25<br>T30<br>T40                                                                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |          |
|                |                  |                                                                                     |  Square           | #1<br>#2                                                                                                                          |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |          |
|                |                  |                                                                                     |  Internal Hex     | 1/4in<br>9/32in<br>5/16in<br>11/32in<br>3/8in<br>7/16in<br>1/2in<br>5.5mm<br>6.0mm<br>7.0mm<br>8.0mm<br>9.0mm<br>10.0mm<br>11.0mm |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |          |

## Drive-Loc Sets - Cont'd

| Part Number           | Number of Pieces | Part Image                                                                          | Type                                                                                               | Tip Size                                                                                                      | Set Includes                                                                                                                                                                                                                                                                                                                                                    | Price    |
|-----------------------|------------------|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| <b><u>WT28189</u></b> | 15               |    |  Phillips         | #1<br>#2                                                                                                      | (1) SoftFinish Drive-Loc VI handle, (14) Drive-Loc VI adjustable/reversible blades (slotted (3.5mm, 4.5mm, 5.5mm, 6.5mm), Phillips (#1, #2), tamperproof torx (T6, T7, T8, T9, T10, T15, T20, T25, T30, T40), hex (2.0mm, 2.5mm, 3.0mm, 4.0mm, 5.0mm, 6.0mm, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in), (1) cushion grip blade lock handle in canvas pouch | \$160.00 |
|                       |                  |                                                                                     |  Slotted          | 3.5mm<br>4.5mm<br>5.5mm<br>6.5mm                                                                              |                                                                                                                                                                                                                                                                                                                                                                 |          |
|                       |                  |                                                                                     |  Tamperproof Torx | T6<br>T7<br>T8<br>T9<br>T10<br>T15<br>T20<br>T25<br>T30<br>T40                                                |                                                                                                                                                                                                                                                                                                                                                                 |          |
|                       |                  |                                                                                     |  External Hex     | 3/32in<br>7/64in<br>1/8in<br>9/64in<br>5/32in<br>3/16in<br>2.0mm<br>2.5mm<br>3.0mm<br>4.0mm<br>5.0mm<br>6.0mm |                                                                                                                                                                                                                                                                                                                                                                 |          |
| <b><u>WT28196</u></b> | 8                |  |  Internal Hex   | 3/16in<br>1/4in<br>5/16in<br>11/32in<br>3/8in<br>7/16in<br>1/2in                                              | (1) SoftFinish Drive-Loc VI handle, (7) Drive-Loc VI adjustable nut setters (3/16in, 1/4in, 5/16in, 11/32in, 3/8in, 7/16in, 1/2in), (1) cushion grip blade lock handle in canvas pouch                                                                                                                                                                          | \$76.00  |
| <b><u>WT28198</u></b> | 8                |  |  Internal Hex   | 5.0mm<br>5.5mm<br>6.0mm<br>7.0mm<br>8.0mm<br>9.0mm<br>10.0mm                                                  | (1) SoftFinish Drive-Loc VI handle, (7) Drive-Loc VI adjustable nut setters (5.0mm, 5.5mm, 6.0mm, 7.0mm, 8.0mm, 9.0mm, 10.0mm), (1) cushion grip blade lock handle in canvas pouch                                                                                                                                                                              | \$71.00  |