

wiha Screwdrivers

Tools that work for you








Standard Screwdrivers

Wiha standard screwdrivers consist of premium-quality tool steel engineered for performance in high-demand environments pros see every day. Each driver blade is precisely heat-treated delivering years of service life, and the driver tips are precision machined for an exact fit, nearly eliminating the potential for fastener head cam-out. SoftFinish® driver handles feature an 8-edged large-diameter comfort grip for maximum gripping area, giving the user powerful torque and less fatigue.

Features














- SoftFinish® cushion grip handle for comfort and control
- Dual durometer construction for long-lasting durability
- Handle direct molded to blade for permanent bond
- Handle sized proportionate to blade for consistent mechanical advantage
- Parallel flats for roll-off prevention
- Tip profile labeled on cap for easy identification
- Exact fit precision machined tip for reduced cam-out



Standard Screwdrivers									
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price
<u>WT31105</u>		<div> Phillips</div>	#0	6.5in (165mm)	2.4in (60mm)	0.12in (3.0mm)	4.1in (104mm)	SoftFinish cushion grip handle	\$4.75
<u>WT31110</u>			#1	7.5in (191mm)	3.1in (80mm)	0.18in (4.6mm)	4.4in (112mm)		\$7.25
<u>WT31115</u>			#2	8.6in (218mm)	3.9in (100mm)	0.24in (6.1mm)	4.7in (119mm)		\$9.50
<u>WT31117</u>				12.5in (318mm)	7.8in (200mm)				\$9.75
<u>WT31118</u>				16.5in (418mm)	11.8in (300mm)				\$13.75
<u>WT31120</u>			#3	10.8in (274mm)	5.9in (150mm)	0.32in (8.1mm)	4.9in (124mm)		\$12.25



Tools that work for you

Standard Screwdrivers - Cont'd											
Part Number	Part Image	Type	Tip Size	Slotted Tip Thickness	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price	
<u>WT30204</u>		 Slotted	3mm	0.5mm	7.2in (184mm)	3.1in (80mm)	0.12in (3.0mm)	4.1in (104mm)	SoftFinish cushion grip handle	\$6.25	
<u>WT30205</u>					8.0in (203mm)	3.9in (100mm)				\$6.25	
<u>WT30210</u>			0.14in (3.5mm)	\$6.50							
<u>WT30211</u>			4.5mm	0.8mm	9.3in (236mm)	4.9in (125mm)	0.18in (4.6mm)	4.3in (109mm)		\$7.25	
<u>WT30215</u>			4mm		8.3in (211mm)	3.9in (100mm)	0.16in (4.0mm)	4.4in (112mm)		\$6.50	
<u>WT30218</u>			4.5mm		7.5in (191mm)	3.1in (80mm)	0.18in (4.6mm)			\$7.00	
<u>WT30220</u>			5.5mm	1.0mm	9.3in (236mm)	4.9in (125mm)	0.22in (5.6mm)	4.3in (109mm)		\$8.00	
<u>WT30265</u>			6.5mm	1.2mm	3.0in (76mm)	3.0in (76mm)	0.26in (6.5mm)	2.0in (50mm)		\$8.75	
<u>WT30223</u>					8.6in (218mm)	3.9in (100mm)		4.7in (119mm)		\$8.75	
<u>WT30225</u>					10.6in (269mm)	5.9in (150mm)				\$9.00	
<u>WT30268</u>			8mm		10.8in (274mm)	0.28in (7.0mm)	\$15.00				
<u>WT53035</u>			10mm	1.6mm	11.6in (293mm)	6.9in (175mm)	0.36in (9.1mm)			\$26.00	

wiha Screwdrivers

Tools that work for you

Standard Screwdriver Sets










Wiha standard screwdrivers consist of premium-quality tool steel engineered for performance in high-demand environments pros see every day. Each driver blade is precisely heat-treated delivering years of service life, and the driver tips are precision machined for an exact fit, nearly eliminating the potential for fastener head cam-out. SoftFinish® driver handles feature an 8-edged large-diameter comfort grip for maximum gripping area, giving the user powerful torque and less fatigue.

Features

- SoftFinish® cushion grip handle for comfort and control
- Dual durometer construction for long-lasting durability
- Handle direct molded to blade for permanent bond
- Handle sized proportionate to blade for consistent mechanical advantage
- Parallel flats for roll-off prevention
- Tip profile labeled on cap for easy identification
- Exact fit precision machined tip for reduced cam-out



WT30277

Standard Screwdriver Sets						
Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
WT30277	5		 Phillips	#1 #2	(5) SoftFinish screwdrivers (Phillips #1, #2, slotted 4.5mm, 6.5mm, 8.0mm)	\$39.00
			 Slotted	4.5mm 6.5mm 8.0mm		
WT30278	7		 Phillips	#1 #2 #3	(7) SoftFinish screwdrivers (slotted: (3.5mm, 4.0mm, 5.5mm, 6.5mm), Phillips (#1, #2, #3))	\$45.00
			 Slotted	3.5mm 4.0mm 5.5mm 6.5mm		
WT30284	14		 Phillips	#0 #1 #2	(12) SoftFinish standard screwdrivers (slotted: (3.0 x 80mm, 3.0 x 100mm, 4.5 x 125mm, 4.5 x 80mm, 4.5 x 150mm, 6.5 x 100mm, 6.5 x 150mm), Phillips: (#0 x 60mm, #1 x 80mm, #2 x 100mm, #2 x 200mm, #2 x 300mm)), (2) SoftFinish stubby screwdrivers (slotted: (6.5 x 25mm), Phillips: (#2 x 25mm))	\$97.00
			 Slotted	3.0mm 4.5mm 6.5mm		