

wiha Wrenches

Tools that work for you

T-handle Sets

Wiha T-handle sets offer T-handles that are designed to endure the harshest environments and applications. The shafts are permanently molded into the handle and have a vibration absorbing inner core. Sets come with either single drive T-handles or dual drive T-Handles. Wiha offers handle types for any environment, including insulated, SoftGrip and classic grip.

Features

- Insulated
 - Individually tested to 10,000 volts AC and rated to 1,000 volts AC for safety and peace of mind
 - Handle molded on for maximum protection
 - Wiha premium quality tool steel for strength and durability
 - Black oxide finish for corrosion protection
 - Exact fit precision machined tip for reduced cam out
 - Meets EN/IEC 60900 testing standards for protection against arc flash explosion
 - Meets ASTM F1505 standard specifications for insulated and insulating hand tools
- SoftGrip Dual Drive
 - SoftGrip Handle for maximum working comfort
 - Dual-Drive - Long Arm Short Arm Drive
 - Dual-Drive T-Handle design for maximum power and versatility
 - Especially useful for loosening or tightening screws that are hard to move
 - Permanent molded on handle with vibration absorbing inner core
 - Ball End option enables fastening and unfastening at an angle of up to 25°
- Classic Grip
 - Color coded for Imperial and metric designations
 - Wiha exclusive Chrome-V-Moly Super Tool Steel
 - Through hardened durability
 - Anti-corrosion nickel finish
 - Molded on Comfort Grip T-Handle
 - Ergo shape for maximum power comfort

**WT33490****WT54095****WT33492**

T-handle Sets							
Part Number	Number of Pieces	Part Image	Type	Tip Size	Insulated	Set Includes	Price
WT33478	5		 External Hex	4mm 5mm 6mm 8mm 10mm	Yes	(5) insulated T-handles (hex: (4.0mm, 5.0mm, 6.0mm, 8.0mm, 10.0mm))	\$60.00
WT33490	6			5/32in 3/16in 7/32in 1/4in 5/16in 3/8in		(6) insulated T-handles (hex: (5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in))	\$72.00
WT33492	10			3/32in 7/64in 1/8in 9/64in 5/32in 3/16in 7/32in 1/4in 5/16in 3/8in	No	(10) comfort grip anti-corrosion T-handles (hex: (3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in))	\$56.00



Tools that work for you

T-handle Sets - Cont'd							
Part Number	Number of Pieces	Part Image	Type	Tip Size	Insulated	Set Includes	Price
<u>WT33493</u>	8		External Hex	2mm 2.5mm 3mm 4mm 5mm 6mm 8mm 10mm	No	(8) Comfort grip anti-corrosion t-handles (hex: (2.0Mm, 2.5Mm, 3.0Mm, 4.0Mm, 5.0Mm, 6.0Mm, 8.0Mm, 10.0Mm))	\$50.00
<u>WT33494</u>	11		Ball-end Hex	5/64in 3/32in 7/64in 1/8in 9/64in 5/32in 3/16in 7/32in 1/4in 5/16in 3/8in		(11) Soft grip dual drive T-handles (ball end hex: (5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in))	\$78.00
<u>WT54095</u>	8			2mm 2.5mm 3mm 4mm 5mm 6mm 8mm 10mm		(8) Soft grip dual drive T-handles (hex: (2.0mm, 2.5mm, 3.0mm, 4.0mm, 5.0mm, 6.0mm, 8.0mm, 10.0mm))	\$86.00
<u>WT54097</u>	10			3/32in 7/64in 1/8in 9/64in 5/32in 3/16in 7/32in 1/4in 5/16in 3/8in		(10) Soft grip dual drive T-handles (hex: (3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in))	\$103.00
<u>WT33496</u>	8			2mm 2.5mm 3mm 4mm 5mm 6mm 8mm 10mm		(8) Soft grip dual drive T-handles (ball end hex: (2.0mm, 2.5mm, 3.0mm, 4.0mm, 5.0mm, 6.0mm, 8.0mm, 10.0mm))	\$66.00