




ENCLOSURE ASSEMBLY TOP VIEW




SECTION B-B
SIDE VIEW




INSIDE BOX VIEW




SECTION A-A
END VIEW



STEEL PANEL
ORDER SEPARATELY



INSIDE LID VIEW



POLYCARBONATE
VERSION ONLY
UL US LISTED
FILE #E65324
TYPE 4,4X,6,6P

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)
Contact Factory (modshop@hammfg.com) for quotes
Solid models of this enclosure available in .stp or .x_t
(Part number and text placement/orientation on our products are subject to change,
we do not recommend using them as a locating reference for modification purposes)

NOTE


Purchased assembly includes styled box, flanged lid, 4 cover screws, and preformed silicone gasket.
General Purpose ABS version is not UL approved. (Matl UL94 - HB)
Polycarbonate version is UL 508 approved. (Matl UL94 - 5VA @ 3mm)

Recommended Cover screw torque -- 2.5 lbf-in (30 cN-m)

1555WF

1555WF Regular Enclosure

General Purpose ABS RAL-7035	1555WF17GY
Polycarbonate RAL-7035	1555W2F17GY
ACCESSORIES	
Steel Inner Panels	1554WPL
Silicone Pre-formed Gasket Black (Pkg 2)	1554WGASKET
Steel Panel / P.C. Board Self Tapping Screw [#4 X 1/4" (6.4mm) Plated]	1555TS100
Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50)	SC576-50



**HAMMOND
MANUFACTURING®**

1555WF17

www.hammondmfg.com

Dimensions:
mm
[inches]