







SENSY SINGLE POINT LOAD CELL, 110 LB/50 KG, +/- 0.3% OF FULL SCALE ACCURACY, CURRENT SIGNAL RANGE(s) OF 4-20 MA, 10-30 VDC, ANODIZED ALUMINUM ALLOY, IP54, 6.5FT/2M INTEGRAL 4-WIRE SHIELDED CABLE

2172L-50KG-A3-K

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
3/12/2025

SHEET 1 OF 1