




LEVER, SIDE-ENTRY, 2 OPENINGS, COPPER CONDUCTOR, 24-12 AWG SOLID,
24-12 AWG STRANDED, 20A, 600V, POLYCARBONATE HOUSING,
TRANSPARENT/ORANGE. PACKAGE OF 10.

WAGO SPLICING CONNECTOR

221-412_K007-0000

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
2/17/2026

SHEET 1 OF 1