




LEVER, SIDE-ENTRY, 5 OPENINGS, COPPER CONDUCTOR, 24-12 AWG SOLID,  
24-12 AWG STRANDED, 20A, 600V, POLYCARBONATE HOUSING,  
TRANSPARENT/ORANGE. PACKAGE OF 10.

## WAGO SPlicing CONNECTOR

221-415\_K006-0000

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
**[inch]**

LATEST VERSION  
2/17/2026

SHEET 1 OF 1