







SENSY TENSION AND COMPRESSION LOAD CELL, 330 LB/150 KG, +/- 0.3% OF FULL SCALE ACCURACY, CURRENT SIGNAL RANGE(s) OF 4-20 MA, 10-30 VDC, ANODIZED ALUMINUM ALLOY, IP54, 9.8FT/3M INTEGRAL 4-WIRE SHIELDED CABLE

2782-150DAN-0.1-B

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

mm  
[inch]

LATEST VERSION  
11/19/2024

SHEET 1 OF 1