



2-WAY, 2-POSITION, N.C., ACETAL BODY, 1/4IN PUSH-TO-CONNECT TUBING INLET(s), 1/4IN PUSH-TO-CONNECT TUBING OUTLET(s), CV=0.24, 150 PSI MAXIMUM OPERATING PRESSURE, 24 VDC OPERATING VOLTAGE, 18IN PIGTAIL.

<b>SPARTAN SOLENOID VALVE</b>		<b>3825-66-B20C-A</b>		AutomationDirect.com 1-800-633-0405	
3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	<b>inch</b> [mm]
					LATEST VERSION 2/6/2023
					SHEET 1 OF 1