



2-WAY, 2-POSITION, N.C., ACETAL BODY, 1/4IN PUSH-TO-CONNECT TUBING INLET(s), 1/4IN PUSH-TO-CONNECT TUBING OUTLET(s), CV=0.31, 75 PSI MAXIMUM OPERATING PRESSURE, 120 VAC OPERATING VOLTAGE, 11mm DIN STYLE WIRING PLUG.

SPARTAN SOLENOID VALVE

3825-67-B20Y-A

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
1/26/2023

SHEET 1 OF 1