



SENSY BENDING BEAM LOAD CELL, 3306 LB/1500 KG, +/- 0.3% OF FULL SCALE ACCURACY, VOLTAGE SIGNAL RANGE(S) OF 1.8-2.2 MV/V, 3-12 VDC, STAINLESS STEEL, IP67, 26.2FT/8M INTEGRAL 4-WIRE SHIELDED CABLE

5510-1.5T-A3-K

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

mm  
[inch]

LATEST VERSION  
11/18/2024

SHEET 1 OF 1