



METAL WORK REGTRONIC PNEUMATIC TRANSDUCER, 4-20 mA, 0-5 VDC OR 0-10 VDC INPUT, 0.05-10 bar ADJUSTABLE OUTPUT PRESSURE, 0-10 VDC, SWITCH (N.O./N.C.) PNP/NPN OUTPUT, 1/8in FEMALE NPT INLET(S), 1/8in FEMALE NPT OUTLET(S), 8-PIN M12 QUICK-DISCONNECT, IP65

5521500U

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
5/15/2023

SHEET 1 OF 1