



WAGO INDUSTRIAL LEAN MANAGED ETHERNET SWITCH, 10 PORTS, (8) ETHERNET GIGABIT (RJ45) AND (2) SFP COMBO GIGABIT PORT(s), MODBUS TCP AND SNMP, -40 TO +60 DEG C, METAL HOUSING, IP30, 35mm DIN RAIL MOUNT

852-1813

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
2/10/2025

SHEET 1 OF 1