



IRONHORSE ACG SERIES AC GENERAL PURPOSE DRIVE, ENCLOSED, 230 VAC, 1/2HP WITH 3-PHASE INPUT, 1/6HP WITH 1-PHASE INPUT, SVC OR V/Hz MODE, A FRAME, RS-485, MODBUS, 100KA SCCR. OPTIONAL ETHERNET/IP AND MODBUS TCP CARD AVAILABLE

**ACG-20P5**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
**[inch]**

LATEST VERSION  
3/27/2024

SHEET 1 OF 1