



CURRENT, VOLTAGE OR FREQUENCY INPUT, POSITIVE BACKLIT LCD
 CONFIGURABLE TO MULTIPLE RGB COLORS, (1) CURRENT OR VOLTAGE AND (2)
 DISCRETE OUTPUTS, 100-240 VAC OPERATING VOLTAGE, MODBUS RTU

TRUMETER ADM200 MULTI-FUNCTION PANEL METER

ADM200-HP-CS

AutomationDirect.com
 1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
11/22/2022

SHEET 1 OF 1