



THIS DRAWING IS THE SOLE AND EXCLUSIVE PROPERTY OF ROBROY ENCLOSURES. NO PART OF THIS DRAWING MAY BE REPRODUCED, DISTRIBUTED OR PUBLICALLY DISPLAYED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS WRITTEN PERMISSION OF ROBROY ENCLOSURES. ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS. COPYRIGHT © 2023 ROBROY ENCLOSURES

SPECIAL REQUIREMENTS				NEMA 250: TYPE 1, 3R, 4, 4X, 6P, 12 IEC 60529 IP66, IP68		STANDARD P/N: AH20164C		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03 .XXX ± 0.010	
ASSEMBLY: 1 (1) POLYCARBONATE ACCESSORY KIT (WPPCACCKITNOFT) SHALL BE PACKAGED LOOSELY INSIDE ENCLOSURE				COLOR: N/A COLOR STANDARD: PANTONE 7541 C		CUSTOMER DWG:							
				MATERIAL: POLYCARBONATE									
				REVISION HISTORY									
				REV	DESCRIPTION	DATE	ENG						
				-	-	-	-						
				-	-	-	-						
				-	-	-	-						
				-	-	-	-						
				-	-	-	-						
				-	-	-	-						
								DRAWN BY AA	DATE 2/9/23	CUSTOMER		DWG AH20164C	
								SCALE DO NOT SCALE		DESCRIPTION STANDARD ENCLOSURE		PART NUMBER ATAH20164C	

**Robroy Enclosures**  
500 Maple Street  
Belding, Michigan 48809  
Phone: 616-794-0700  
Fax: 616-749-3378

