



Motor Connector



SECTION A-A'

SIGNAL	PIN No.	WIRE COLOR
U	A	Red
V	B	White
W	C	Blue
FG	D	Grn/Yel

CABLE PART#	LENGTH 'L'(m)	LENGTH 'L'(ft)
APCS-PN03JS-AD	3m	9.8ft
APCS-PN05JS-AD	5m	16.4ft
APCS-PN10JS-AD	10m	32.8ft
APCS-PN20JS-AD	20m	65.6ft
APCS-PF03JS-AD	3m	9.8ft
APCS-PF05JS-AD	5m	16.4ft
APCS-PF10JS-AD	10m	32.8ft
APCS-PF20JS-AD	20m	65.6ft

LS ELECTRIC POWER FLEX CABLE, MATING CONNECTORS, 32.8ft/10m CABLE LENGTH, FOR USE WITH 230 VAC APM-FF55D AND APM-FF75D MOTORS WITHOUT BRAKE

APCS-PF10JS-AD

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

mm  
[inch]

LATEST VERSION  
3/9/2022

SHEET 1 OF 1