



FINGER-SAFE, 310A, 1-POLE, LINE SIDE: 1 OPENINGS ACCEPT 350 MCM TO 6 AWG CU/AL, LOAD SIDE: 12 OPENINGS ACCEPT 4 AWG TO 14 AWG CU/AL, DIN RAIL OR PANEL MOUNT, UL 1953 LISTED.

## PENN UNION OPEN POWER DISTRIBUTION BLOCK

APDB-112-350-1

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR  
PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

inch  
[mm]

LATEST VERSION  
6/25/2024

SHEET 1 OF 1