



FINGER-SAFE, 350A, 1-POLE, LINE SIDE: 2 OPENINGS ACCEPT 2/0 AWG TO 14 AWG CU/AL, LOAD SIDE: 2 OPENINGS ACCEPT 2/0 AWG TO 14 AWG CU/AL, DIN RAIL OR PANEL MOUNT, UL 1953 LISTED.

PENN UNION OPEN SPLICER/REDUCER BLOCK

ASRB-22-2_0-1

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
6/25/2024

SHEET 1 OF 1