



Color and Length Part Number Combinations

C6A-CMRSTPnn-Sxx

| nn | Color | Sxx | Length | Tolerance |
|----|-------|-----|--------|-----------|
| BL | Blue | S1 | 1FT | ±9.84% |
| | | S3 | 3FT | ±3.28% |
| | | S7 | 7FT | ±1.87% |
| | | S10 | 10FT | ±1.64% |
| | | S14 | 14FT | ±1.17% |
| | | S25 | 25FT | ±0.66% |
| | | S50 | 50FT | ±0.66% |

Notes:

1. CABLE – UL Type CMR, 23AWG*4P + AE, OD: 6.2MM, Rated 60°C
2. RJ45 8P8C Shielded Plug
3. Minimum Bending Radius: 48MM [1.88"]
4. Operating Temperature: 0–60°C [32–140°F]

| C6A-CMRSTPnn-Sxx | |
|---|----------------|
| Rev: A | Date: 2/3/2026 |
| Units: mm [inches] | |
| Scale: 1:1 | |
| Cat 6A CMR Ethernet Patch Cable | |
|  | |