



LAUMAS LOW PROFILE COMPRESSION LOAD CELL, 22040 LB/10000 KG, +/- 0.03% OF FULL SCALE ACCURACY, VOLTAGE SIGNAL RANGE(S) OF 2 MV/V, 3-15 VDC, STAINLESS STEEL, IP68, 16.4FT/5M INTEGRAL 6-WIRE SHIELDED CABLE

CBL10000

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
11/5/2024

SHEET 1 OF 1