



LAUMAS LOW PROFILE COMPRESSION LOAD CELL, 550 LB/250 KG, +/- 0.03% OF FULL SCALE ACCURACY, VOLTAGE SIGNAL
 RANGE(s) OF 2 MV/V, 3-15 VDC, STAINLESS STEEL, IP68, 16.4FT/5M INTEGRAL 6-WIRE SHIELDED CABLE

CBL250

AutomationDirect.com
 1-800-633-0405



3rd
 ANGLE

NOT TO
 SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
 DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
 FOR PART DESIGN

UNLESS OTHERWISE
 SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
 11/5/2024

SHEET 1 OF 1