



DOVETAIL, PNP, N.O. OUTPUT, 5-28 VDC OPERATING VOLTAGE, LED INDICATION, 9.8FT (3.00m) 3-WIRE PIGTAIL WITH WIRE LEADS, STRAIGHT CABLE ENTRY, 1/4IN 60 DEGREE DOVETAIL SLOT MOUNT, FOR POSITION SENSING.

NITRA CYLINDER SWITCH

CPS9E-AP-A

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
5/22/2024

SHEET 1 OF 1