



PROSENSE INDUCTIVE PROXIMITY SENSOR, RECTANGULAR, 80 X 40 X 92MM BODY, POLYPHENYLENE ETHER HOUSING, PNP, N.O. OUTPUT, 50MM SENSING DISTANCE, FLUSH, 70 HZ SWITCHING FREQUENCY, IP67, 4-PIN M12 QUICK-DISCONNECT.

D80-AP-3H

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
2/28/2023

SHEET 1 OF 1