



ISOMETRIC VIEW

CONTRINEX INDUCTIVE PROXIMITY SENSOR, TUBULAR, 30MM DIAMETER X 83MM BODY, 304 STAINLESS STEEL HOUSING, PNP, N.O., 15MM SENSING DISTANCE, NON-FLUSH, 150 HZ SWITCHING FREQUENCY, IP67, PIGTAIL.

**DW-HD-613-M30-411**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
9/29/2022

SHEET 1 OF 1