




| PIN NUMBER | WIRE COLOR | SIGNAL |
|------------|------------|--------|
| 1 | BLACK | 0VDC |
| 2 | RED | +VDC |
| 3 | YELLOW | A |
| 4 | BLUE | /A |
| 5 | GREEN | B |
| 6 | ORANGE | /B |
| 7 | WHITE | NC |
| 8 | GREY | NC |
| CASE | SHIELD | SHIELD |



LIKA ELECTRONIC ENCODER CABLE, M12 AXIAL FEMALE TO PIGTAIL, SHIELDED, 16.4FT/5M CABLE LENGTH, FOR USE WITH LIKA ELECTRONIC AR01 SERIES MEASURING WHEEL ENCODER ASSEMBLIES

EC-M12F8-LKM8-05

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
10/29/2024

SHEET 1 OF 1