


PIN NUMBER	WIRE COLOR	SIGNAL
1	BRAID	SHIELD
2	RED	+5VDC
3	BLACK	0VDC
4	BROWN	CAN_H
5	BLUE	CAN_L



LIKA ELECTRONIC ENCODER CABLE, M12 AXIAL FEMALE TO PIGTAIL, SHIELDED, TWISTED PAIR, 32.8FT/10M CABLE LENGTH, FOR USE WITH LIKA ELECTRONIC MODBUS RTU ENCODERS

EC-M12FC-LKCB-10

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

mm  
[inch]

LATEST VERSION  
9/10/2024

SHEET 1 OF 1