



KNOCKOUTS ON TOP
AND BOTTOM




11.8
[0.46]

1" - 1.25"
[35 - 44MM]
KNOCK OUT


0.5" - 0.75"
[22 - 28.5MM]
KNOCK OUT





190.0
[7.48]



141.6
[5.57]



25.0
[0.98]



50A, 3-POLE, 120 VAC (50/60Hz) COIL VOLTAGE, THERMAL
OVERLOAD, 32.0-50.0A ADJUSTABLE, NEMA 1.

WEG ELECTRIC ESW MANUAL MOTOR STARTER

ESW-B50D15A-R71

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
1/18/2023

SHEET 1 OF 1