



KNOCKOUTS ON TOP  
AND BOTTOM






11.8  
[0.46]


1" - 1.25"  
[35 - 44MM]  
KNOCK OUT



0.5" - 0.75"  
[22 - 28.5MM]  
KNOCK OUT



Ø 7.0  
[0.28]



25.0  
[0.98]

Ø 7.0  
[0.28]

80A, 3-POLE, 120 VAC (50/60Hz) COIL VOLTAGE, THERMAL  
OVERLOAD, 63.0-80.0A ADJUSTABLE, NEMA 1.

WEG ELECTRIC ESW MANUAL MOTOR STARTER

ESW-B80D15A-R75

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

mm  
[inch]

LATEST VERSION  
1/18/2023

SHEET 1 OF 1