



LAUMAS BENDING BEAM LOAD CELL, 165 LB/75 KG, +/- 0.017% OF FULL SCALE ACCURACY, VOLTAGE SIGNAL RANGE(s) OF 2 MV/V, 3-15 VDC, STAINLESS STEEL, IP68, 9.8FT/3M INTEGRAL 4-WIRE SHIELDED CABLE

FCAL75

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
11/5/2024

SHEET 1 OF 1