



35mm DIN RAIL MOUNT, 6-32 VDC INPUT VOLTAGE, SPST, (1) N.O. SCR, 90A CONTACT RATING, 24-600 VAC LOAD VOLTAGE, PUSH-IN SPRING, OVERVOLTAGE AND THERMAL PROTECTION, EXTERNAL 115 VAC REQUIRED. THERMAL/LOAD INTERRUPTION ALARM.

GEFRAN SOLID STATE RELAY

GRSH-90-60-D-2-61

AutomationDirect.com
1-800-633-0405

3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE: mm [inch]	LATEST VERSION 4/4/2024	SHEET 1 OF 1
-----------	--------------	---	-----------------------------------	--	----------------------------	--------------