



2-PORT (2-WAY), 2-POSITION, N.C., STAINLESS STEEL BODY, VITON/PTFE SEAL(s), 1/4IN FEMALE NPT INLET(s), 1/4IN FEMALE NPT OUTLET(s), CV=1.1, 0 PSI MINIMUM OPERATING PRESSURE, 120 VAC OPERATING VOLTAGE, 18mm DIN STYLE WIRING PLUG.

**GC VALVES - SOLENOID VALVE**

**H401YH02Z1BF5**

AutomationDirect.com  
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	<b>inch</b> <b>[mm]</b>	LATEST VERSION 12/15/2025	SHEET 1 OF 1
--	-----------	--------------	---	---------------------------------	---------------------------------------	----------------------------	------------------------------	--------------