






VIEW A-A



BLUE ANODIZED ALUMINUM, RECTANGULAR, 3000 PSI MAXIMUM OPERATING PRESSURE, (4) STATIONS, 3/4IN FEMALE NPT INLET(S), 1/8IN FEMALE NPT OUTLET(S), 45-DEG AND 135-DEG ORIENTATION.

CITCO AIR, COOLANT, OIL OR WATER MANIFOLD

IM3-4-BD-8-1-8-N-B

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
9/18/2024

SHEET 1 OF 1