





VIEW A-A



RED ANODIZED ALUMINUM, RECTANGULAR, 3000 PSI MAXIMUM OPERATING PRESSURE, (6) STATIONS, 3/4IN FEMALE NPT INLET(S), 1/8IN FEMALE NPT OUTLET(S), 45-DEG AND 135-DEG ORIENTATION.

CITO AIR, COLLANT, OIL OR WATER MANIFOLD

IM3-6-BD-12-1-8-N-R

AutomationDirect.com  
1-800-633-0405



3rd ANGLE

NOT TO SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR PART DESIGN

UNLESS OTHERWISE SPECIFIED UNITS ARE:

inch [mm]

LATEST VERSION 9/18/2024

SHEET 1 OF 1