





VIEW A-A



RED ANODIZED ALUMINUM, RECTANGULAR, 3000 PSI MAXIMUM OPERATING PRESSURE, (8) STATIONS, 1IN FEMALE NPT INLET(s), 1/4IN FEMALE NPT OUTLET(s), 45-DEG AND 135-DEG ORIENTATION.

CITO AIR, COOLANT, OIL OR WATER MANIFOLD

IM4-11-BD-16-1-4-N-R

AutomationDirect.com
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	inch [mm]	LATEST VERSION 9/18/2024	SHEET 1 OF 1
--	-----------	--------------	---	---------------------------------	---------------------------------------	----------------------------	-----------------------------	--------------