



BLUE ANODIZED ALUMINUM, RECTANGULAR, 3000 PSI MAXIMUM OPERATING PRESSURE, (4) STATIONS, 1IN FEMALE NPT INLET(s), 1/4IN FEMALE NPT OUTLET(s), 45-DEG AND 135-DEG ORIENTATION.

**CITO AIR, COOLANT, OIL OR WATER MANIFOLD**

**IM4-6-BD-8-1-4-N-B**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR  
PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

inch  
[mm]

LATEST VERSION  
9/18/2024

SHEET 1 OF 1