



RED ANODIZED ALUMINUM, RECTANGULAR, 3000 PSI MAXIMUM OPERATING PRESSURE, (4) STATIONS, 1IN FEMALE NPT INLET(s), 3/8IN FEMALE NPT OUTLET(s), 45-DEG AND 135-DEG ORIENTATION.

**CITO AIR, COOLANT, OIL OR WATER MANIFOLD**

**IM4-6-BD-8-3-8-N-R**

AutomationDirect.com  
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	<b>inch</b> <b>[mm]</b>	LATEST VERSION 9/18/2024	SHEET 1 OF 1
--	-----------	--------------	---	---------------------------------	---------------------------------------	----------------------------	-----------------------------	--------------