



BLUE ANODIZED ALUMINUM, RECTANGULAR, 3000 PSI MAXIMUM OPERATING PRESSURE, (8) STATIONS, 1-1/2IN FEMALE NPT INLET(S), 1/2IN FEMALE NPT OUTLET(S), 45-DEG AND 135-DEG ORIENTATION

CITO AIR, COOLANT, OIL OR WATER MANIFOLD

IM6-18-BD-16-1-2-N-B

AutomationDirect.com
1-800-633-0405

3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE: inch [mm]	LATEST VERSION 9/18/2024	SHEET 1 OF 1
-----------	--------------	---------------------------------------------------------------------	---------------------------------	--------------------------------------------------------	-----------------------------	--------------