



INTERNATIONAL POWER UNREGULATED LINEAR POWER SUPPLY, 48 VDC @ 10A/480W, 120/240 VAC NOMINAL
INPUT, 1-PHASE, OPEN FRAME, ALUMINUM HOUSING, CHASSIS MOUNT, SCREW AND SPADE.

IP500U48

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
5/18/2023

SHEET 1 OF 1