



IronHorse MTR SERIES STANDARD EFFICIENCY AC INDUCTION MOTOR, CENTRIFUGAL JET PUMP, 1/3HP, 1-PH, 115/230 VAC, 3600RPM, TEFC, 56J FRAME, ROLLED STEEL, REMOVABLE BASE/C-FACE MOUNT

**MTRJ-P33-1AB36J**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR  
PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

inch  
[mm]

LATEST VERSION  
4/26/2022

SHEET 1 OF 1