



2-PORT (2-WAY), 2-POSITION, N.C., LEAD-FREE BRASS BODY, EPDM RUBBER SEAL(s),  
 3/8IN FEMALE NPT INLET(s), 3/8IN FEMALE NPT OUTLET(s), CV=4.3, 120 VAC  
 OPERATING VOLTAGE, 8W, NSF/ANSI 61.

## GC VALVES POTABLE WATER SOLENOID VALVE

**NS711YH02C9CG1**

AutomationDirect.com  
 1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
 DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR  
 PART DESIGN

UNLESS OTHERWISE  
 SPECIFIED UNITS ARE:

**inch**  
**[mm]**

LATEST VERSION  
 2/18/2025

SHEET 1 OF 1