



2-PORT (2-WAY), 2-POSITION, N.O., LEAD-FREE BRASS BODY, EPDM RUBBER SEAL(s), 3/8IN FEMALE NPT INLET(s), 3/8IN FEMALE NPT OUTLET(s), CV=4.3, 120 VAC OPERATING VOLTAGE, 8W, NSF/ANSI 61.

GC VALVES POTABLE WATER SOLENOID VALVE

NS712YH02C9CG1

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
2/18/2025

SHEET 1 OF 1