



2-PORT (2-WAY), 2-POSITION, N.O., LEAD-FREE BRASS BODY, EPDM RUBBER SEAL(S), 1-1/4IN FEMALE NPT INLET(S), 1-1/4IN FEMALE NPT OUTLET(S), CV=22, 120 VAC OPERATING VOLTAGE, 8W, NSF/ANSI 61.

GC VALVES POTABLE WATER SOLENOID VALVE

NS712YH02C9GJ2

AutomationDirect.com
1-800-633-0405

3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE: inch [mm]	LATEST VERSION 2/18/2025	SHEET 1 OF 1
-----------	--------------	---	---------------------------------	--	-----------------------------	--------------