



OPTRIS CSlaser 2M INFRARED PYROMETER, 385-1600 DEG C, 1.6 µm SPECTRAL RANGE, 4-20mA AND ALARM OUTPUT, 5-30 VDC OPERATING VOLTAGE, M48x1.5 THREADED END MOUNT, REMOVABLE SCREW TERMINAL PLUG

OPTCSL2MHSF

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
7/18/2023

SHEET 1 OF 1